

# **Product Data Sheet**



## MPB SERIES 1200BV-ANS/230 ANAESTHETIC VARIABLE AREA FLOWMETER

#### **GENERAL INFORMATION**

This version of the MPB Series 1200BV-ANS/230 Flowmeter is manufactured exclusively to house an anaesthetic 230mm standard length flow tube and will give an instantaneous flow rate of the standard anaesthetic gases.

The MPB Series 1200BV-ANS/230 Anaesthetic Flowmeter has an overall length of 300mm, with process centres of 275mm.

This flowmeter can be supplied with either straight through, or rear facing connections ( $G\frac{1}{4}$ ").

The anaesthetic flow tube supplied with this instrument is fully compliant to ISO 5358 and BS4272.

Normally the flow tube supplied exhibits dual scale calibration whereby the first third of the flow range is dedicated to 0.1-1 L/min and, for example, 2-10 L/min would be a linear scale for the remainder of the scale length.

Please see page 2 of this technical bulletin for flow ranges and gases available with this flowmeter.

The 1200BV-ANS/230 Anaesthetic Flowmeter is supplied with an integral flow control valve.

The flowmeter has a photo luminescent backing to provide a degree of back lighting in the event of power failure.

The flow tube is fully conductive, both internally and externally, and is compliant to the international standard for human and veterinary anaesthesia flow measurement.

The flow tube utilises serial numbered floats and flow tubes to guard against incorrect reassembly when cleaning. In addition, the float exhibits a white dot so that the operator can clearly see the rotation.

The flow tube is supplied complete with colour banding to international standards. We can also supply colour banding to other requirements.

The flowmeter is fitted with a contact device to earth the flow tube through to the mounting studs and chassis. This is to prevent any static build up.

In addition to standard anaesthetic gases, MPB can supply calibrated flow tubes for xenon, heliox, entinox, nitrox and nitric oxide as typical examples.

The 1200 Series Flowmeter has nickel plated brass end connections, however, stainless steel can be supplied if required at an additional cost.




MPBTB 095 Iss 3 Page 1 of 2

### MPB SERIES 1200BV-ANS/230 ANAESTHETIC VARIABLE AREA FLOWMETER

#### **FEATURES**

- VALVED OR NON-VALVED VERSIONS
- STRAIGHT THROUGH OR REAR FACING CONNECTIONS
- FRICTIONLESS, HENCE LOW HEAD LOSS
- ELEGANT AND ROBUST DESIGN
- EASY TO READ SCALE
- EASY IN-SITU TUBE REMOVAL AND RE-INSTALLATION
- STANDARD OR CUSTOMISED FLOW SCALES AVAILABLE
- DIRECT READING OF INSTANTANEOUS FLOW RATE
- POLYCARBONATE SAFETY COVER
- MINIMAL MAINTENANCE
- COLOUR BANDING TO INTERNATIONAL STANDARD (SPECIFY WHEN ORDERING)
- LONG SERVICE LIFE



STANDARD RANGES	
Flow Rate	Gas
100 - 1000cc/min 0.1 - 1 L/min 0.1 - 4 L/min 0.1 - 8 L/min 0.1 - 10 L/min 0.2 - 12 L/min 0.2 - 15 L/min 1 - 10 L/min	O2, Air, CO <sub>2</sub> , N <sub>2</sub> O O2, Air, CO <sub>2</sub> , N <sub>2</sub> O O2, CO <sub>2</sub> , N <sub>2</sub> O O2, Air, CO <sub>2</sub> , N <sub>2</sub> O O2, Air, CO <sub>2</sub> , N <sub>2</sub> O O2, Air, CO <sub>2</sub> , N <sub>2</sub> O Air, CO <sub>2</sub> , N <sub>2</sub> O O2, Air O2, Air, CO <sub>2</sub> , N <sub>2</sub> O

Chassis: Anodised aluminium to

**BSEN12373** 

End Blocks: Nickle plated Brass

**Stainless Steel** 

**Process** 

Connections: G1/4" rear facing or straight

through

Valve Stem: Stainless steel, Cover: Polycarbonate

Seals: Viton

Metering Tube: Borosilicate glass 230mm long

with permanently fired scale and fully conductive to ISO 5358 and

**BS 4272** 

Scale: Permanently fired (black)

Weight: 670 grams

Plumb Bob Floats: Red hard anodised

aluminium with white rotation indicator

**Maximum Working** 

Pressure: Gas: up to 20 bar g

(non shock)

NOTE: All flow tubes calibrated at

1013 mbar abs 20°C

**Maximum Working** 

Temperature: 100°C Viton

Accuracy: All flow tubes supplied with

this instrument have been calibrated to confirm their accuracy falls within the limits set by ISO 5358 and Class 2.5 VDI/VDE 3513. All calibration equipment is traceable to National UK Standards

Customised flow ranges are available.

Please consult MPB Industries to select the required flow range for the process fluid used.

MPB Industries Ltd - Designers and Manufacturers of Scientific and Process Control Instrumentation

Part of the Scientific Digital Imaging plc (SDI) group of companies
Unit 1 Branbridges Ind Est, East Peckham, Kent TN12 5HF, UK, Tel: +44 (0)1622 872401
mail@mpbflowmeters.com, www.mpbflowmeters.com

SDIGROUP

Due to the constant development and improvement of products, information may be altered or withdrawn without notice.

MPBTB 095 Iss 3 Page 2 of 2